

Digital Refractometers

Brix / Salinity / Glycol or Customized Scales

- ◆ *Refractive Index*
- ◆ *Coffee and Beverages*
- ◆ *Fruit Juices and Sap*
- ◆ *Wine and Beer*
- ◆ *Ethanol / Alcohol*
- ◆ *Clinical*
- ◆ *Syrups*
- ◆ *Honey*
- ◆ *Brines*
- ◆ *Concentrates*
- ◆ *Automotive*
- ◆ *Lubricants*
- ◆ *and More*



MSDR-P2 Professional Series



LH Economy Series

Model	MSDR-P2-50 Low Range Brix	MSDR-P2-90 High Range Brix	LH-T95 High Range Brix	LH-A28 Salinity (NaCl)
RI	1.3330 ~ 1.4200 (±0.0003)	1.3330 ~ 1.5318 (±0.0003)	1.333 ~ 1.540 (±0.005)	1.333 ~ 1.410 (±0.003)
Brix	0 ~ 50% (±0.2%)	0 ~ 90% (±0.2%)	0 ~ 95% (±0.5%)	×
Salinity	Optional (NaCl)		×	NaCl 0~28% (±0.2%)
Glycol	Optional (°C or %V)		×	×
Customize	<p><i>Please consult us for full list of options</i></p> <p>Examples: Honey Water/Baume, Wort, Beer Plato, Wine, Fructose, Glucose, Urine, IPA, Urea, Battery Fluid, ADBLue, Sea Water</p>		×	×
Resolution	0.1% / 0.1°C / 0.0001 RI		0.1% / 0.1°C / 0.001 RI	
Calibration	Zero Point with Pure or Distilled Water			
Operating	0°C ~ 60°C		10°C ~ 40°C	
ATC	0°C ~ 60°C (±0.5°C)		10°C ~ 60°C (±0.5°C)	
Sample	Minimum volume ≥ 0.2 mL		Minimum volume ≥ 0.3 mL	
Sensor	High accuracy, Anti-Loss design Inhibits external light interference		Standard	
Display	1.8" Colour LCD		Two line Blue LED	
Dimension	120 x 58 x 26mm / 125g		154 x 52 x 44mm / 140g	
Power	Internal Rechargeable Battery		2 x AAA Alkaline Batteries	
Included	Hard carry case, USB charging cable, protective rubber boot with sensor cover, dropper and manual		Storage Box, dropper, batteries and manual	

Distributor:

AWR Smith Process Instrumentation cc

PO Box 449 Pinegowrie 2123

Tel: 011 782 7279 / 888 7144 WhatsApp Messaging: 087 255 6713

e-mail: sales@instruments.co.za website: www.instruments.co.za